



Grade: CGF

Description: A metallic/holographic foil suitable for textile application.

Application: Test the foil onto fabric without the adhesive in order to see whether the foil adheres onto the fabric without using adhesive. The foil will come off after initial washing without using adhesive.

Once it has been determined that adhesive will be needed in applying the foil you will need the following

Have a silkscreen made with the decal artwork desired. Stamp the foil onto the fabric using a flat-faced die. Use regular normal stamping procedure or apply vinyl-water-based adhesive on a release paper. Put it face down onto the fabric. Stamp the release paper, using a metal die onto the fabric, when pulled off it leave the adhesive on the fabric.

Micron: 23

Working temperature: Vertical 120 – 140 °C

Dwell Time: 15 Seconds

This should just be used as guidance due to the fact that the temperature is directly related to speed of machinery.

Manufactured widths: 610mm

Please note that this information should be used as a guide only and not as a guarantee of suitability due to the wide variety of substrates and working methods used. We would recommend that a foil sample is tested prior to purchase. We endeavour to keep our foils in stock however please be advised that stock levels do fluctuate depending on demand and we therefore recommend that you contact the office for up to date stock information prior to ordering.

Product Data Sheet V.1.0.1

Date Issued 22.03.2021

Office Controlled

Foilco
Enterprise Way
Lowton St Mary's
Warrington
Cheshire
WA3 2BP
United Kingdom

Phone +44 (0) 1942 262 622
Enquiries hello@foilco.com
Twitter foilco
Instagram foilcoltd
Visit foilco.com

